

Miele 60cm Built-in Ovens

Model Overview

Miele Built-in Oven DNA

**20
YEARS**

Miele Quality

German engineered and tested to the equivalent of 20 years average usage.



PerfectClean Enamel

Thanks to its high glass content and non-stick properties, cleaning your cavity and baking trays is made simple.



Miele Made Electronics

Allows easy serviceability and unique operation of the product.



CoolTouch Door

The door on all Miele ovens will remain cool to the touch even during high pyrolytic temperatures.



CleanGlass Door

The door and inner glass panels on all Miele ovens can be easily removed for cleaning.



FlexiClip Runners


All Miele 60cm ovens come with a pair of full extension FlexiClip runners, which makes removing trays and baking dishes simple.

2000 series models



	H 2267-1 B	H 2267-1 BP	H 2860 B	H 2860 BP
Capacity	76 l	76 l	76 l	76 l
Display / Controls	EasyControl	EasyControl	EasyControl	EasyControl
Cooking Functions	8	7	8	7
Interior Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel
Catalytic Liner / Pyrolytic Cleaning	YES / -	- / YES	YES / -	- / YES
Pyrofit Accessories	-	-	-	-
Door Construction	Triple Glazing	Quadruple Glazing	Triple Glazing	Quadruple Glazing
SoftOpen / SoftClose	-	-	YES / YES	YES / YES
Halogen Light / LED	YES / -	YES / -	YES / -	YES / -
Accessories Supplied				
Baking tray	x1	x1	x1	x1
Multi-purpose tray	x1	x1	x1	x1
Grilling and roasting insert	-	-	x1	x1
Wire racks	x2	x2	x2	x2
Flexi-clips	x1	x1	x1	x1
Available Design Lines				
ContourLine - CleanSteel	-	-	H 2760 B	H 2760 BP
PureLine - CleanSteel	✓	✓	✓	✓
VitroLine - GG¹ / OBSW / BRW¹	-	-	-	✓ / ✓ / ✓
ArtLine (Handle-less) - GG¹ / OBSW / BRW¹	-	-	-	-

Miele's Built-in Oven Quality Pledge









✓ 10-year quality assurance against the corrosion on CleanSteel fascia and door panel.

✓ 10-year quality assurance against the crazing or cracking of the internal liner/cavity.



Miele 60cm Built-in Ovens

Model Overview

7000 series models							
	H 7260 BP	H 7264 BP	H 7464 BP	H 7464 BPX	H 7660 BP	H 7860 BP	H 7860 BPX
Capacity	76 l	76 l	76 l	76 l	76 l	76 l	76 l
Display / Controls	DirectSensor S	DirectSensor S	DirectSensor	DirectSensor	M Touch S	M Touch	M Touch
Cooking Functions	9	11	14	14	17	17	17
Interior Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel	PerfectClean Enamel
Catalytic Liner/Pyrolytic Cleaning	- / YES	- / YES	- / YES	- / YES	- / YES	- / YES	- / YES
Pyrofit Accessories	-	-	YES	YES	YES	YES	YES
Door Construction	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing	Quadruple Glazing
SoftOpen / SoftClose	YES / YES	YES / YES	YES / YES	YES / -	YES / YES	YES / YES	YES / -
Automatic Programmes	25 programmes	25 programmes	50 programmes	50 programmes	>150 programmes	>150 programmes	>150 programmes
User Programmes	20 programmes	20 programmes	20 programmes	20 programmes	20 programmes	20 programmes	20 programmes
Moisture Plus	-	YES	YES	YES	YES	YES	YES
Crisp Function	-	-	YES	YES	YES	YES	YES
TasteControl	-	-	YES	YES	YES	YES	YES
Corded Food Probe / Wireless Food Probe	-	-	YES / -	YES	YES / -	- / YES	- / YES
FoodView	-	-	-	-	-	YES	YES
Appliance Networking (Wi-Fi)	-	YES	YES	YES	YES	YES	YES
SuperVision Display	-	-	-	-	YES	YES	YES
MotionReact	-	-	-	-	YES	YES	YES
Halogen Light / LED	- / YES	- / YES	- / YES	- / YES	- / YES	- / YES	- / YES
Accessories Supplied							
Baking tray	x1	x1	x1	x1	x1	x1	x1
Multi-purpose tray	x1	x1	x1	x1	x1	x1	x1
Grilling and roasting insert	x1	x1	x1	x1	x1	x1	x1
Wire racks	x2	x2	x2	x2	x2	x2	x2
Flexi-clips	x1	x1	x1	x1	x1	x1	x1
Available Design Lines							
ContourLine - CleanSteel	-	H 7164 BP	-	-	-	-	-
PureLine - CleanSteel	✓	✓	✓	-	✓	✓	-
VitroLine - GG¹ / OBSW / BRW¹	-	✓ / ✓ / ✓	✓ / ✓ / ✓	-	✓ / ✓ / ✓	✓ / ✓ / ✓	-
ArtLine (Handle-less) - GG¹ / OBSW / BRW¹	-	-	-	✓ / ✓ / ✓	-	-	✓ / ✓ / ✓